



## TMA - WAW-1000B Electro-hydraulic Servo-controlled Universal Testing Machine



I Equipment name: Electro-hydraulic servo-controlled universal testing machine.

#### II Model: TMA - WAW-1000B

#### III Usages and characteristics:

This machine adopts the electro-hydraulic servo technology, the automatic controlling of the testing force, displacement, speed by the microcomputer, and the full implementation of automation from the experimental data acquisition to processing and printing, the test can be carried out. Highly effective in accordance with national standard of GB228-2002, the sample



folder adopts hydraulic chuck; it is easy to operate, safe and reliable. It cannot carry out the conventional tests of material pulling, pressing, bending, shear, it also provides a wide range of attachment necessary for the special testing.

#### $\ensuremath{\operatorname{IV}}$ The main technical parameters:

- 1. Max. test power: 1000KN
- 2. Number of columns: four column
- 3. Measuring range: 4%~100%FS (full range)
- 4. Accuracy class: 1 class
- 5. Relative Error of Indicating Value:  $\leq \pm 1\%$
- 6. Test Force Resolution: 0.1KN
- 7. Deformation Measuring Range: 4% to 100% of extensometer scale
- 8. Deformation Error Value:  $\leq \pm$  1% of indicating value
- 9. Deformation Resolution: 0.001mm
- 10. Displacement error value:  $\leq \pm 1\%$
- 11. Displacement resolution: 0.01mm
- 12. Clamping method: Hydraulic
- 13. Piston Max. Stroke: 200mm
- 14. The piston max. movement speed:50mm/min
- 15. Distance between two columns: 580mm
- 16. Max. Tensile Space: 600mm
- 17. Max. Compression Space: 500mm



- 18. Max. Flat Sample Clamping Width: 75mm
- 19. Flat Sample Clamping Thickness: 0-15mm
- 20. Round Sample Clamping Diameter: Ø13~Ø40mm
- 21. Compression Plate Size:  $\Phi$  208mm
- 22. Bending Test Roller Space: 400mm
- 23. Bending Test Roller Width: 140mm
- 24. Bending Pressure Head Diameter:  $\phi 40$
- 25. The host machine overall dimension:  $(890 \times 660 \times 2300)$  mm
- 26. Weight: About 3000Kg
- 27. Voltage: 415V/50Hz 2.5kW

### V Performance characteristics:

First: Mechanical process structures

The host of the oil cylinder underneath type, chain transmission and hydraulic clamping, tensile space is located in the upper part of the host, compression, bending, shear test space is located in the main beam and between table; Oil source part adopts Piano desktop hydraulic oil source.

 The table and beams using cast steel materials, post and screw use and 40Cr quenching and tempering, rigid.

2. Cylinder with special process, honing processing, clearance seal, seal is extremely strong, long service life.

3. Import ATOS electro-hydraulic servo valve, imported high pressure oil pump, low noise, smooth operation.



4. Oil source using steel plate forming with plastic-sprayed surface treatment, marble mesa can place the computer and printer, clean and tidy, save space.

Second: Control and Measurement System

The control and measurement system of this machine adopts the advanced technology of testing industry. With the electro-hydraulic closed loop control and measuring system, which can finish the uniform stress, constant strain, constant test force, constant displacement, test force keeping, displacement keeping, etc. This system has multiple protection function, which can realize the protection to overload, overflowing, overvoltage, under-voltage, overrun and limit, etc.

This system is equipped with professional measurement software, which can deal with the statistics and data processing, and can calculate the upper and lower yield point, tensile strength, breaking strength, elastic modulus, elongation,  $\sigma 0.2$ , etc. It shows the force, displacement, stress etc and the dynamic display of test curve during the whole test process, and also it can change between the test-time, test-displacement, displacement-time, and the test reports and curves can be output.

1. The classification management user permissions, the user login, according to its authority to open the corresponding operation function module;

2. Using the most advanced multi-threading technology to collect data,



# Test Machines Australia

speed, rate stability, and a variety of anti-interference processing of sensor data, to avoid accidental acquisition failed control failure defects;

3 Has a powerful report editing features, the user can according to their own requirements for the preparation of the test report, output the various needs of the result, the data can also use Word format for easy editing;

4. Database management automatically save all test data and curves, and has curve enlarge, compare and times refer function for the laboratory network to provide a quality basis.

· 模式 设置 调整 工具 會口 帮助 退出 共打开助概1条,当前位整力1,编号:/	は「存置き One 2 はな 分析 影響の			(Cit B)	R 200m T	
		MED XSHT		(10): 克克(m) 0.0 利用(u)	46270	臣 (15 (m))
	575 (m) 0.0 D • 😂 🔖 🖬 🞇 🔅	× 🏼 🙂 · 🏦 📜 📕	## C	13.8840 1196		-3.240
	记录位置/记录总数: 14 4	1/1 • •	800. Clut	10.0mm	■ 程控	
	试样报号: //110	Det d			2 KWR	
5000W 2500W 1000W 500W 25nn 12 5nn	5mm 2.5mm \$2.5mm	100 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	SQ BEAD R			
10	村長 /			in rollant	221	1.0 m/nin
	2 9 合 巨 10 は約日期 2005-10-25	700				
	the second secon	<u> </u>			designed in the second	
00 - <del>7</del> 01	and the second se					在标准度 (m/nin)
	王 は私人:/ ●  は和人:/ 目対				1.05	6.1 0.2 0.5 1
		<u> </u>			s	10 20 50 300
	试样尺寸[直径(m)]					
∞ - <u>/ \</u>	Se (ma*2): 0.000	La (ma) : 0				
····	Lu(m) 0	Lo (ma):  0 A (%):  0				
∞- \\	Sq(m <sup>2</sup> 2) 0	Z (%): 0 300-			and the second se	
	7e 040 3.99500	10 00 a):				
»-	The second se	2.4.02.0				
w_ 1/2		Kal. (97 a)			es (	(RBNE)
w/*	79.040 2.40250	lo ma) n-				
	71.030	31.02.0			\$	
0.0 -	107.0	An (%): 0	140 280 420 580	700 040 800 1,520 1 #DRco	1,200 1,400	TR BAN RE
000 - 244	1 1 1 Ag(%)	Agt (%)		REM(x)		

#### VI Configuration Introduction:

1.The host (1000kN cylinder down-setting)	one
2. The electric-hydraulic servo oil source	one
3. Electric-hydraulic servo valve - imported	one
4. Oil pressure sensor	one
5. High-pressure oil pump - imported	one
6. Manual control box	one
7. Extensometer	one
8. Lenovo computer	one





9. Color inkjet printer	one
10. Computer observe and control software	one
11. Special data acquisition card	one
12. Attachment	
1) Tensile fixture (Round jaw $\Phi$ 13- $\Phi$ 26,	$\Phi$ 26- $\Phi$ 40 Flat jaw 0-15,
15-30)	each one
2) Compression fixture $\Phi 208mm$	one set
3) Bending fixture ( $\Phi$ 40mm)	one set
13. Foundation bolt	four

For further information please contact:



0418 369 505 sales@testmachines.com.au www.testmachines.com.au