

TMA - WEW-600B Computer Screen Hydraulic Universal Testing Machine



I Equipment name: Computer Screen Hydraulic Universal Testing Machine

II Model: TMA - WEW-600B

III Usages and characteristics:

WEW-600B series of computer screen hydraulic universal testing machine is mainly used for testing of metal materials, non-metallic materials, mechanical properties, it can meet the latest national standard for users' testing and data analysis, and widely used in scientific research institutes, tertiary institutions, industrial and mining enterprises, technical supervision, commodity inspection studying department.

IV The main technical parameters:

1. Max. test power: 600KN

2. Number of columns: four column

3. Measuring range: 2%~100%FS (full range)

4. Accuracy class: 1 class

5. Relative Error of Indicating Value: $\leq \pm 1\%$

6. Test Force Resolution: 0.1KN

7. Deformation Measuring Range: 2% to 100% of extensometer scale

8. Deformation Error Value: $\leq \pm 1\%$ of indicating value

9. Deformation Resolution: 0.001mm

10. Displacement error value: $\leq \pm 1\%$

11. Displacement resolution: 0.01mm

12. Clamping method: Hydraulic

13. Piston Max. Stroke: 200mm

14. The piston max. movement speed: 50mm/min

15. Distance between two columns: 500mm

16. Max. Tensile Space: 600mm

17. Max. Compression Space: 500mm

18. Max. Flat Sample Clamping Width: 70mm

19. Flat Sample Clamping Thickness: 0-15mm

20. Round Sample Clamping Diameter: Ø6~Ø40mm

21. Compression Plate Size: ⊕188mm

22. Bending Test Roller Space: 120mm

23. Bending Test Roller Width: 140mm

24. Bending Pressure Head Diameter: Φ 30

25. The host machine overall dimension: $(820 \times 620 \times 2150)$ mm

26. Weight: About 2400Kg

27. Voltage: 415V/50Hz

V Performance characteristics:

First: Mechanical process structures

The host of the oil cylinder underneath type, chain transmission and hydraulic clamping, tensile space is located in the upper part of the host, compression, bending, shear test space is located in the main beam and between table; Oil source part adopts Piano desktop hydraulic oil source.

1. The table and beams using cast steel materials, post and screw use and 40Cr quenching and tempering, rigid.

- 2. Cylinder with special process, honing processing, clearance seal, seal is extremely strong, long service life.
- 3. With high pressure oil pump, low noise, smooth operation.
- 4. Oil source using steel plate forming with plastic-sprayed surface treatment, marble mesa can place the computer and printer, clean and tidy, save space.

Second: Control and Measurement System

The control and measurement system of this machine adopts the advanced technology of testing industry, electro-hydraulic closed loop control and measuring system. This system has multiple protection function, which can realize the protection to overload, overflowing, overvoltage, under-voltage, overrun and limit, etc.

This system is equipped with professional measurement software, which can deal with the statistics and data processing, and can calculate the upper and lower yield point, tensile strength, breaking strength, elastic modulus, elongation, $\sigma 0.2$, etc. It shows the force, displacement, stress etc. and the dynamic display of test curve during the whole test process, and also it can change between the test-time, test-displacement, displacement-time, and the test reports and curves can be output.

- 1. The classification management user permissions, the user login, according to its authority to open the corresponding operation function module;
- 2. Using the most advanced multi-threading technology to collect data, speed, rate stability, and a variety of anti-interference processing of sensor data, to avoid accidental acquisition failed control failure defects;
- 3 Has a powerful report editing features, the user can according to their own requirements for the preparation of the test report, output the various needs of the result, the data can also use Word format for easy editing;
- 4. Database management automatically save all test data and curves, and has curve enlarge, compare and times refer function for the laboratory network to provide a quality basis.

VI Configuration Introduction:

1.The host (600kN cylinder down-setting)	one
2. The hydraulic oil source	one
3. Oil pressure sensor	one
4. High-pressure oil pump	one
5. Manual control box	one
6. Extensometer	one
7. Lenovo computer	one
8. Color inkjet printer	one
9. Computer observe and control software	one
10. Special data acquisition card	one
11. Attachment	
1) Tensile fixture (Round jaw Φ 13- Φ 26、 Φ 26- Φ 40 Flat jaw 0-15)	each one
2) Compression fixture Φ188mm	one set
3) Shearing fixture (Φ 30mm)	one set
12. Foundation bolt	four

For further information please contact:



0418 369 505 sales@testmachines.com.au www.testmachines.com.au